

Features

- Contemporary design
- Single lever handle allows for both on/off activation and temperature setting
- Red/blue indexing on handle
- 3-9/15" (91 mm) spout height
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Laminar flow
- Includes pop-up drain with lift rod and tailpiece
- Coordinates with other products in the Taut™ collection to complete your bathroom

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- G 1/2 inlet connection
- Single-hole installation
- Deck-mount



Codes/Standards

None Applicable

KOHLER® One-Year Warranty – Mexico


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	BL	Matte Black
---	----	-------------



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.32 gal/min (5 l/min)

Drain included: Yes

Spout:

Spout reach: 3-15/16" (100 mm)

Notes

Install this product according to the installation instructions.