

Features

- Contemporary design
- Single Lever handle provides on/off activation and volume control
- For use with cold water line only
- 3-15/16" (100 mm) spout reach
- 3-1/2" (89 mm) spout height
- 1.5 gpm (5.7 lpm) maximum flow rate at 65 psi 4.5 bar)
- Aerated flow
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Drain sold separately
- Coordinates with other products in the Taut™ collection to complete your bathroom

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing


Installation

- G 1/2 inlet connection
- Single-hole installation
- Deck-mount

**Codes/Standards**

Plumbing Standards
TIS 2067-2552

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.189 gal/min (4.5 l/min)

Drain with overflow: Yes

Spout:

Spout reach: 3-15/16" (100 mm)