

## Features

- Quarter-turn washerless ceramic disc valves
- Pop-up drain with lift rod and tailpiece
- Standard aerator
- Variety of handle style options
- 5-1/4" (133 mm) gooseneck spout
- Lower flow aerator options are available
- 8" (203 mm) to 16" (406 mm) centers
- 0.5 gpm (1.9 lpm) maximum flow rate at 60 psi (4.14 bar)

## Material

- Brass valve bodies
- Brass

## Required Products/Accessories

[K-16010-3](#) Cross Handles for Centerset Base Faucet

or

[K-16010-4](#) Lever Handles for Centerset Base Faucet

or

[K-16010-5](#) Wristblade Lever Handles for Centerset Base Faucet

## Recommended Products/Accessories

K-23726 Drain treatment

K-23723 Faucet cleaner

## Optional Products/Accessories

1160595 .35 gpm Aerator, Medium



## Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations


DOE - Energy Policy Act 1992

California Energy Commission (CEC)

IAPMO Certification

## KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

### Faucet:

Flow rate: 0.5 gal/min (1.9 l/min)

Drain included: Yes

Drain tailpiece included: Yes

### Spout:

Spout reach: 5-1/4" (133 mm)

## Notes

Install this product according to the installation guide.