

## Features

- Quarter-turn washerless ceramic disc valves
- Less drain and lift rod
- Standard aerator
- Variety of handle style options
- Less handles
- 2.0 gpm (7.6 lpm) maximum flow rate at 60 psi (4.14 bar)

## Material

- Brass
- Brass valve bodies

## Required Products/Accessories

[K-16012-3](#) Cross Handles for Widespread Base Faucet

## Recommended Products/Accessories

K-23723 Faucet cleaner

## Optional Products/Accessories

1160594 .35 gpm Aerator, Large




## Codes/Standards

ASME A112.18.1/CSA B125.1  
NSF/ANSI/CAN 61  
NSF/ANSI/CAN 372  
All applicable US Federal and State material regulations  
DOE - Energy Policy Act 1992  
IAPMO Certification

## KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: No

#### Spout:

Spout reach: 5" (127 mm)

### Notes

Install this product according to the installation guide.