Geometric | K-7517

Touchless single-hole lavatory faucet with Insight™ sensor technology and temperature mixer, HES-powered, 0.5 gpm

Features

- 0.5 gpm (1.9 lpm) maximum flow rate
- Factory-set 30-second maximum continual run cycle
- Vandal-resistant aerator
- 24" (610 mm) flexible supply hose for easy installation
- Less drain
- Includes 3.6 volt Hybrid Energy Cell

Sustainability

WATER-SAVING DESIGN

Available Colors/Finishes

Color tiles intended for reference only.

CP Polished Chrome
VS Vibrant Stainless

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-27-2026 05:03 - US-CA

THE BOLD LOOK OF KOHLER

KOHLER. Touchless single-hole lavatory faucet with Insight™ sensor technology and temperature mixer, HES-powered, 0.5 gpm

Codes/Standards

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

ADA | CSA B651 | OBC

ASME A112.18.1/CSA B125.1
NSF/ANSI/CAN 372
DOE - Energy Policy Act 1992
ADA
ICC/ANSI A117.1
CSA B651
OBC

Technical Information

All product dimensions are nominal.

Spout

Spout Reach:	5-3/8" (136 mm)

Flow Rate

Faucet Flow Rate:	0.5 gpm (1.9 l/min)

Material

- Brass

Recommended Products/Accessories

- [object Object]23726 Drain treatment
- K-23723 Faucet cleaner

Optional Products/Accessories

- 1351966 Cache Pca Spray, 0.35Gpm
- 1101643 Cache Spray 0.5 Gpm
- 1139288 Cache Aerated, 1.0 Gpm
- 1139289 Cache Laminar, 1.0 Gpm
- 1139290 Cache Aerated, 1.5 Gpm
- 1100596 Cache Std, M24 X 1 Pca Laminar
- K-13478-A 4" escutcheon plate for Insight™ and Kinesis® faucet
- K-13478-B 4" escutcheon plate for Insight™ and Kinesis® faucet
- K-13479-A 8" escutcheon plate for Insight™ and Kinesis® faucet
- K-13479-B 8" escutcheon plate for Insight™ and Kinesis® faucet
- K-7129 Bathroom sink grid drain without overflow
- K-7129-A Bathroom sink grid drain with overflow

Technology

- Electronic Insight™ sensor technology for accurate and consistent activation

Warranty

See website for detailed warranty information.

KOHLER® One-Year Limited Warranty

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-27-2026 05:03 - US-CA

THE BOLD LOOK OF KOHLER.



Installation

- Single-hole mounting
- Above-counter valve for easy installation and maintenance

Installation Notes

Install this product according to the installation instructions.

A 1-1/4" (32 mm) minimum to 1-1/2" (38 mm) maximum diameter mounting hole is required.
The minimum distance between the back of the faucet spout and the wall must be 1-3/4" (44 mm). This will allow proper clearance for setscrew access.
The maximum distance between the bathroom sink basin edge to the base of the faucet spout must be 1-3/4" (44 mm).
The maximum height of the lip basin should be 3/4" (19 mm).
Product includes rosebud spray aerator. Other aerator styles are available.
ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
10-27-2026 05:03 - US-CA
THE BOLD LOOK OF KOHLER.