

### Features

- 0.5 gpm (1.9 lpm) maximum flow rate
- Factory-set 30-second maximum continual run cycle
- Vandal-resistant aerator
- 24" (610 mm) flexible supply hose for easy installation
- 6-3/16" (157 mm) spout reach
- Less drain

### Material

- Brass

### Technology

- Includes 3.6 volt Hybrid Energy Cell
- Electronic Insight™ sensor technology for accurate and consistent activation

### Installation

- Single-hole mounting
- Above-counter valve for easy installation and maintenance

### Recommended Products/Accessories

K-23723 Faucet cleaner

### Optional Products/Accessories

1160593 .35 gpm Aerator, Small  
 1139286 Small Aerated 1.0 gpm (3.8 l/min)  
 1139287 Small Laminar 1.0 gpm (3.8 l/min)  
 1053576 Small Aerated 1.5 gpm (5.7 l/min)  
 1053532 Small Laminar 1.5 gpm (5.7 l/min)  
 78783 Sealing Washer  
 K-7129 Drain  
 K-7129-A Bathroom sink grid drain with overflow  
 K-13478-A 4" escutcheon plate for Insight™ and Kinesis® faucet  
 K-13478-B 4" escutcheon plate for Insight™ and Kinesis® faucet  
 K-13479-A 8" escutcheon plate for Insight™ and Kinesis® faucet  
 K-13479-B 8" escutcheon plate for Insight™ and Kinesis® faucet



ADA

CSA B651

OBC

### Codes/Standards



ASME A112.18.1/CSA B125.1  
 NSF/ANSI/CAN 372  
 All applicable US Federal and State material regulations  
 DOE - Energy Policy Act 1992  
 California Energy Commission (CEC)  
 ADA  
 ICC/ANSI A117.1  
 CSA B651  
 OBC  
 IAPMO Certification


### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	VS	Vibrant® Stainless



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 0.5 gal/min (1.9 l/min)

Drain included: No

#### Spout:

Spout reach: 6-1/16" (154 mm)

#### Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

### Notes

Install this product according to the installation guide.

A 1-1/4" (32 mm) minimum to 1-1/2" (38 mm) maximum diameter mounting hole is required.

The minimum distance between the back of the faucet spout and the wall must be 1-3/4" (44 mm). This will allow proper clearance for setscrew access.

The maximum distance between the bathroom sink basin edge to the base of the faucet spout must be 1-3/4" (44 mm).

The maximum height of the lip basin should be 3/4" (19 mm).

Product includes rosebud spray aerator. Other aerator styles are available.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.