



WAVE | K-7528

Touchless hybrid 0.125 gpf washdown urinal flushometer

Features

- Fixture-mount design
- Includes a 30-year hybrid energy cell



DISCONTINUED



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 01:22 - US-CA

THE BOLD LOOK
OF **KOHLER**

Codes/Standards

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

ADA CSA B651 OBC

ASME A112.18.1/CSA B125.1

CSA B64

CSA B125.3

ASSE 1037/ASME A112.1037/CSA B125.37

ADA

ICC/ANSI A117.1

CSA B651

OBC

Pressure/Fixture Supply Requirements

Minimum Flowing Pressure: 25 psi (172.4 kPa)

Minimum Flow Rate: 10 gpm (37.9 l/min)

Material

- Brass

Recommended Products/Accessories

K-23723 Faucet cleaner

Technology

- Electronic infrared sensor with WAVE technology for accurate activation
- Slow-closing piston technology

Warranty

See website for detailed warranty information.


KOHLER® One-Year Limited Warranty



1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications. For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 01:22 - US-CA

*10-3/4" (273 mm) minimum with a
6" (152 mm) critical level above the fixture



Installation

- Intended for urinal installations with 3/4" (19 mm) spud coupling connection

Installation Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.

