

KOHLER® Faucets

Single-handle bathroom sink faucet, cold only, 27.0 lpm

July™
K-75377IN-4

Features

- Versatile modern design
- Single Lever handle provides on/off activation and volume control
- For use with cold water line only
- 90 mm (3.5 inch) spout reach
- 75 mm (2.95 inch) spout height
- Aerated flow
- 27.0 lpm (7.13 gpm) maximum flow rate at 3.0 bar (43.5 psi)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Single-hole installation
- Deck-mount



Codes/Standards

None Applicable

KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel

KOHLER[®] Faucets

Single-handle bathroom sink faucet, cold only, 27.0 lpm
July™
K-75377IN-4



Technical Information

All product dimensions are nominal.

Spout:

Spout reach: 3-9/16" (90 mm)

Notes

Install this product according to the installation instructions.