



All-In-One 33" top-/undermount double-bowl kitchen sink K-75791-2PC

Features

- 1.8 gpm (6.8 lpm) maximum flow rate at 60 psi (4.14 bar)
- Two faucet holes
- 9" (229 mm) depth provides generous workspace
- With Malleco™ pull-down kitchen faucet with soap/lotion dispenser in Vibrant Stainless

Material

- Premium 18-gauge stainless steel

Installation

- Top-mount or undermount

Recommended Products/Accessories

- K-3129 Sink rack for Undertone® and Verse™ kitchen sinks
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-3132 Sink rack for Undertone® and Verse™ kitchen sinks

Optional Products/Accessories

- K-9000 P-Trap

Included Components

- K-R562-SD Pull-down kitchen sink faucet with two-function sprayhead




Codes/Standards

- ASME A112.19.3/CSA B45.4
- ASME A112.18.1/CSA B125.1
- NSF/ANSI/CAN 61
- NSF/ANSI/CAN 372
- DOE - Energy Policy Act 1992
- California Energy Commission (CEC)

KOHLER® Faucet Lifetime Limited Warranty KOHLER® One-Year Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 36" (914 mm)

Bowl area (Right): Length: 14-3/16" (360 mm)
Width: 15-11/16" (398 mm)
Bowl depth: 9" (229 mm)
Water depth: 9" (229 mm)

Bowl area (Left): Length: 14-3/16" (360 mm)
Width: 18-7/16" (468 mm)
Bowl depth: 9" (229 mm)
Water depth: 9" (229 mm)

Number of deck holes: 2

Faucet hole(s): 1-7/16" (37 mm)

Soap/Lotion hole: 1-7/16" (37 mm)

Drain hole: 3-3/4" (94 mm)

Template: Top-mount, 1263722-7, required, included

Notes

Install this product according to the installation instructions.