



**Verse™**  
33" top-/undermount double-bowl kitchen sink  
**K-75791-3**

**Features**

- 36" minimum base cabinet width
- Large/medium bowls
- 9" (229 mm) depth provides generous workspace
- Three faucet holes
- Includes installation hardware

**Material**

- Premium 18-gauge stainless steel

**Installation**

- Top-mount or undermount

**Recommended Products/Accessories**

- K-3129 Sink rack for Undertone® and Verse™ kitchen sinks
- K-8801 Sink drain and strainer with tailpiece
- K-8799 Sink drain and strainer basket
- K-3132 Sink rack for Undertone® and Verse™ kitchen sinks
- K-23726 Drain treatment
- K-23729 Stainless steel cleaner

**Optional Products/Accessories**

- K-11352 Disposal Flange with Stopper




**Codes/Standards**

- ASME A112.19.3/CSA B45.4
- IAPMO Certification

**KOHLER® Stainless Steel Sinks**

**Lifetime Limited Warranty**

See website for detailed warranty information.



## Technical Information

All product dimensions are nominal.

Basin configuration: Large Bowl on Left

Min. base cabinet width: 36" (914 mm)

Bowl area (Right):  
 Length: 14-3/16" (360 mm)  
 Width: 15-11/16" (398 mm)  
 Bowl depth: 9" (229 mm)  
 Water depth: 9" (229 mm)

Bowl area (Left):  
 Length: 14-3/16" (360 mm)  
 Width: 18-7/16" (468 mm)  
 Bowl depth: 9" (229 mm)  
 Water depth: 9" (229 mm)

Number of deck holes: 3

Faucet hole(s): 1-7/16" (37 mm)

Soap/Lotion hole: 1-7/16" (37 mm)

Drain hole: 3-3/4" (94 mm)

Template: 1263722-7, required, included

## Notes

Install this product according to the installation instructions.