

Features

- Diverter spout
- Spout reach is 7-1/4" (184 mm)
- Single lever handle allows for both temperature and volume control
- 13.4 gpm (50.7 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Shift™+ handshower includes a push-button transition between full-coverage and targeted massage sprays, each enhanced with Katalyst™ air-induction technology for an indulgent showering experience
- Thumb tab allows for a smooth transition between sprays
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 2.5 gpm (9.5 lpm) handshower maximum flow rate at 80 psi (5.5 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with Stance faucets, accessories, and showering components to complete your bathroom

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- Three-hole installation
- G 1/2 inlet connection

Recommended Products/Accessories


K-23723 Faucet cleaner



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Drain included: No

Handshower:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Pressure: 80 psi (5.5 bar)

Notes

Install this product according to the installation instructions.