

Features

- Modern, simplistic exposed thermostatic valve serves as a hub for bath/shower controls
- Thermostatic valve allows user to set and maintain precise temperature
- Antiscald protection
- Volume control valve provides on/off operation, along with precise control of water volume and intensity
- Diverter spout
- Rainduet™ handshower provides three spray experiences: full coverage with Katalyst™ air-induction technology, Champagne, and massage
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- Thumb tab allows for a smooth transition between sprays
- Includes 59" (1500 mm) shower hose and holder
- 2.64 gpm (12.0 lpm) maximum flow rate at 80 psi (5.5 bar)

**Codes/Standards**

Plumbing Standards
QB/T 2806

See website for detailed warranty information.

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Technology

- Thermostatic technology automatically maintains temperature within +/- 0.4°C (+/- 0.72°F) during water pressure fluctuations

Installation

- Wall-mount
- G 1/2 inlet connection

Required Products/Accessories

K-8593 72" Shower Hose

or

K-9514 60" Shower Hose

or



K-45981 72" ribbon hose

or

K-45982 60" ribbon hose

Recommended Products/Accessories

K-23723 Faucet cleaner



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 4.5 gal/min (17 l/min)

Drain included: No

Spout:

Spout reach: 8-3/16" (208 mm)

Handshower:

Rated maximum flow: 2.64 gal/min (10 l/min)