

KOHLER® Faucets

600 mm x 800 mm three-function rainhead, 23.2 – 29.4 lpm
K-77276IN-L

Features

- Versatile modern design
- Advanced spray engine provides three spray experiences: full coverage rain with Katalyst air-induction technology, laminar stream, and kinetic massage
- Full coverage rain with Katalyst™ air-induction technology delivers a drenching spray experience, ideal for rinsing shampoo from hair
- Laminar flow
- Massage spray: Targeted, pulsing streams of water massage and ease muscles
- Integrated warm white lights powered by the water flow
- Flexible, silicone nozzles assure long life and easy clean
- Rain spray: 6.1 gpm (23.2 lpm) maximum flow rate at 43.5 psi (3.0 bar) without regulator
- Laminar spray: 7.8 gpm (29.4 lpm) maximum flow rate at 43.5 psi (3.0 bar) without regulator
- Kinetic massage spray: 6.7 gpm (25.5 lpm) maximum flow rate at 43.5 psi (3.0 bar) without regulator
- For simultaneous showerhead functions, a higher flow rate is required

Material

- Premium material construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Technology

- Katalyst™ air-induction technology infuses water with air, creating bigger drops for a more powerful spray

Installation

- Ceiling-mount
- Installation hardware included



Codes/Standards

None Applicable




KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	BV	Vibrant® Brushed Bronze
	RGD	Vibrant Rose Gold

**Technical Information**

All product dimensions are nominal.

Shower/Rainhead rated max flow: 3 gal/min (11.4 l/min)

Notes

Install this product according to the installation instructions.