

Features

- Ergonomic, easy clean design
- Optimized sprayface for maximum performance
- Precision flow control meets all user needs regardless of your home's water pressure
- 2.25 gpm (8.5 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- Includes 47.24 inch (1200 mm) hose and wall-mount holder

Material

- Premium material construction for durability and reliability
- Antimicrobial silicone material

Installation

- G 1/2 inlet connection
- Wall-mount



Codes/Standards

None Applicable


KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Handshower:

Rated maximum flow: 3 gal/min (11.4 l/min)

Notes

Install this product according to the installation guide.