

### Features

- Single pin handle allows for both volume and temperature control
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- Tall height is ideal for vessel-style sinks
- 7" (178 mm) spout reach
- 7-7/8" (201 mm) spout height
- 1.5 gpm (5.7 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes metal pop-up drain with 1-1/4" metal tailpiece
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- For single-hole installation
- G 1/2 inlet connection
- Preattached flexible supply lines simplify installation

### Recommended Products/Accessories

K-23726 Drain treatment  
K-23723 Faucet cleaner




### Codes/Standards

Plumbing Standards  
TIS 2067-2552  
GB 18145

### KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 45 psi (3.1 bar)

Drain included: Yes

Drain with overflow: Yes

#### Spout:

Spout reach: 7" (178 mm)

### Notes

Install this product according to the installation instructions.