

KOHLER® Faucets Tower single-handle bathroom sink faucet with Tube

spout and Pin handle, 5.7 lpm
K-77960T-4A

Features

- Single pin handle allows for both volume and temperature control
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- Tall height is ideal for vessel-style sinks
- 7" (178 mm) spout reach
- 10-5/8" (270 mm) spout height
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)
- Includes metal pop-up drain with 1-1/4" metal tailpiece
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- For single-hole installation
- G 1/2 inlet connection
- Preattached flexible supply lines simplify installation

Recommended Products/Accessories

K-23726 Drain treatment
K-23723 Faucet cleaner



Codes/Standards


Plumbing Standards
GB 18145

See website for detailed warranty information.

KOHLER Faucets Tower single-handle bathroom sink faucet with Tube spout and Pin handle, 5.7 lpm

Components™

K-77960T-4A



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 7" (178 mm)

Notes

Install this product according to the installation instructions.