

### Features

- Tall height is ideal for vessel-style sinks
- Laminar flow delivers a graceful stream of water
- 6-13/20" (169 mm) spout reach
- 10-1/8" (257 mm) spout height
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- For use with Components™ Lever, Oyl, or Industrial faucet handles (sold separately)
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom

### Material

- Premium metal construction for durability and reliability
- KOHLER<sup>®</sup> finishes resist corrosion and tarnishing

### Installation

- Deck-mount
- G 1/2 inlet connection
- Flexible supply lines simplify installation

### Recommended Products/Accessories


- K-23726 Drain treatment
- K-23723 Faucet cleaner



### Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 17 gal/min (64.4 l/min)

Drain included: Yes

Drain with overflow: Yes

#### Spout:

Spout reach: 6-5/8" (169 mm)

### Notes

Install this product according to the installation instructions.