

KOHLER[®] Faucets

Tall bathroom sink faucet spout with Ribbon design,
7.0 lpm
K-77966T

Features

- Tall height is ideal for vessel-style sinks
- Laminar flow delivers a graceful stream of water
- 6-13/20" (169 mm) spout reach
- 10-1/4" (260 mm) spout height
- 1.85 gpm (7.0 lpm) maximum flow rate at 60 psi (4.14 bar)
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- For use with Components™ Lever, Oyl, or Industrial faucet handles (sold separately)
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom

Material

- Premium metal construction for durability and reliability
- KOHLER[®] finishes resist corrosion and tarnishing

Installation

- Deck-mount
- G 1/2 inlet connection
- Flexible supply lines simplify installation

Recommended Products/Accessories

K-23726 Drain treatment
K-23723 Faucet cleaner



Codes/Standards


Plumbing Standards
GB 18145

See website for detailed warranty information.

KOHLER Faucets

Tall bathroom sink faucet spout with Ribbon design,
7.0 lpm
K-77966T

Components™



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 17 gal/min (64.4 l/min)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 6-5/8" (169 mm)

Notes

Install this product according to the installation instructions.