

Features

- Spout reach is 6-5/16" (160 mm)
- 6-11/16" (170 mm) spout height
- For use with Components™ Lever, Oyl, or Industrial faucet handles (sold separately)
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom

Material


- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Deck-mount
- G 1/2 inlet connection

Recommended Products/Accessories


K-23726 Drain treatment
K-23723 Faucet cleaner

**Codes/Standards**

General Acceptance (GA)

KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: Yes

Drain with overflow: Yes

Spout:

Spout reach: 6-5/16" (160 mm)

Notes

Install this product according to the installation instructions.