

### Features

- Aerated flow delivers a smooth, steady stream of water
- 6-13/20" (169 mm) spout reach
- 7" (178 mm) spout height
- 1.2 gpm (4.5 lpm) maximum flow rate at 60 psi (4.14 bar)
- Includes clicker drain with 1-1/4" (32 mm) metal tailpiece
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom
- For use with Components™ Lever, Oyl, or Industrial faucet handles (sold separately)

### Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

### Installation

- Deck-mount
- G 1/2 inlet connection
- Flexible supply lines simplify installation

### Recommended Products/Accessories


K-23726 Drain treatment  
K-23723 Faucet cleaner



### Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty  
information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 1.85 gal/min (7 l/min)

Drain included: Yes

Drain with overflow: Yes

#### Spout:

Spout reach: 6-5/8" (169 mm)

### Notes

Install this product according to the installation instructions.