

Features

- Two lever handles offer separate control of hot and cold water
- 9-5/8" (244 mm) spout reach
- 18 gpm (68 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes Shift™ Ellipse wand multifunction handshower and 59" (1500 mm) shower hose
- Multifunction handshower offers full coverage and targeted massage spray settings
- Full Coverage with Katalyst™ air-induction technology delivers a drenching spray experience, ideal for rinsing shampoo from hair
- 2.2 gpm (8.3 lpm) maximum handshower flow rate at 45 psi (3.1 bar)
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Floor-mount
- G 1/2 inlet connection
- Requires floor-mount bath filler mounting base (sold separately)

Required Products/Accessories

For freestanding installation
K-97339 Mounting block for select floor-mount bath fillers

Recommended Products/Accessories

K-23723 Faucet cleaner








Codes/Standards


Plumbing Standards
GB 18145

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	RGD	Vibrant Rose Gold
	TT	Vibrant Titanium



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 18 gal/min (68.1 l/min)

Drain included: No

Spout:

Spout reach: 9-5/8" (244 mm)

Handshower:

Rated maximum flow: 2.2 gal/min (8.3 l/min)

Notes

For use with automatic compensating valves rated at 2.2 gal/min (8.3 l/min) or less.

Install this product according to the installation instructions.