

# KOHLER<sup>®</sup> Faucets

Wall-mount bath faucet with Tube spout and Lever handles  
**Components™**  
handles  
**K-78014T-4**

## Features

- Two traditional lever handles allow for both volume and temperature control
- Red/blue indexing
- Spout reach is 9-1/2" (241 mm)
- 18 gpm (68 lpm) maximum flow rate at 45 psi (3.1 bar)
- Nondiverter spout
- KOHLER<sup>®</sup> ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with Components faucets, accessories, and showering components to complete your bathroom

## Material

- Premium metal construction for durability and reliability
- KOHLER<sup>®</sup> finishes resist corrosion and tarnishing

## Installation

- Wall-mount
- G 1/2 inlet connection
- Three-hole installation

## Recommended Products/Accessories


K-23723 Faucet cleaner



## Codes/Standards

Plumbing Standards  
GB 18145

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 18 gal/min (68.1 l/min)

Drain included: No

Drain with overflow: Yes

### Notes

Install this product according to the installation instructions.