

Features

- Brass construction and valve bodies
- Vandal-resistant laminar outlet
- Quarter-turn washerless ceramic disc valves
- Less drain
- Lever handles
- 5-3/16" (132 mm) gooseneck spout
- 1.0 gal/min (3.8 l/m) maximum flow rate at 60 psi (4.14 bar).

Installation

- For 8" – 16" (203 – 406 mm) centers

Recommended Products/Accessories

K-23723 Faucet cleaner



ADA

CSA B651

OBC

Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

EPA WaterSense®

ADA

ICC/ANSI A117.1

CSA B651

OBC

IAPMO Certification

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

