

Features

- 1.28 gpf (4.8 lpf)
- 125-micron filter protects internal components
- High back pressure vacuum breaker
- Locking stop cap and nonhold open design provide protection against vandalism
- No external flush volume adjustment ensures water conservation
- Chloramine and chlorine resistance on all rubber components exposed to waterway

Material

- Brass construction with durable Polished Chrome finish

Technology

- Double seal handle design for long life without leaks
- Patented piston technology for superior flush volume accuracy
- Nonhold open piston technology for accurate activation

Installation

- For toilet installations with 1-1/2" top spud coupling connection
- Can be installed for left- or right-handed users

Recommended Products/Accessories

- K-23723 Faucet cleaner
- 1421939 Flushometer Arm Extension Kit
- 1509698 Pressure Gauge Kit, 1/8"



ADA

CSA B651

OBC

Codes/Standards

ASSE 1037/ASME A112.1037/CSA B125.37
EPA WaterSense®
ADA
ICC/ANSI A117.1
CSA B651
OBC
IAPMO Certification

KOHLER® One-Year Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
-------	------	-------------

	CP	Polished Chrome
---	----	-----------------

*10-3/4" (273 mm) minimum with a 6" (152 mm) critical level above the fixture



Technical Information

All product dimensions are nominal.

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

Pressure/fixture Supply Requirements

Fixture pressure max (static): 80 psi (551.6 kPa)
 Fixture pressure min (static): 35 psi (241.3 kPa)
 Min flowing pressure: 25 psi (172.4 kPa)
 Min flow rate: 25 gpm (94.6 lpm)

Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.