

### Features

- 0.5 gpf (1.9 lpf)
- 125-micron filter protects internal components
- High back pressure vacuum breaker
- Locking stop cap and nonhold open design provide protection against vandalism
- No external flush volume adjustment ensures water conservation
- Chloramine and chlorine resistance on all rubber components exposed to waterway

### Material

- Brass construction with durable Polished Chrome finish

### Technology

- Double seal handle design for long life without leaks
- Patented piston technology for superior flush volume accuracy
- Nonhold open piston technology for accurate activation

### Installation

- For urinal installations with 3/4" top spud coupling connection
- Can be installed for left- or right-handed users

### Recommended Products/Accessories

- K-23723 Faucet cleaner
- 1421939 Flushometer Arm Extension Kit
- 1509698 Pressure Gauge Kit, 1/8"



ADA	CSA B651	OBC
-----	----------	-----

### Codes/Standards

ASSE 1037/ASME A112.1037/CSA B125.37  
EPA WaterSense®  
ADA  
ICC/ANSI A117.1  
CSA B651  
OBC  
IAPMO Certification

### KOHLER® One-Year Limited Warranty


See website for detailed warranty information.

### Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome

\*10-3/4" (273 mm) minimum with a  
6" (152 mm) critical level above the fixture



### Technical Information

All product dimensions are nominal.

### Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

### Pressure/fixture Supply Requirements

Fixture pressure max (static): 80 psi (551.6 kPa)  
 Fixture pressure min (static): 25 psi (172.4 kPa)  
 Min flowing pressure: 25 psi (172.4 kPa)  
 Min flow rate: 10 gpm (37.9 lpm)

### Notes

Install this product according to the installation instructions.

ADA, OBC, CSA B651 compliant when installed to the specific requirements of these regulations.