



Chess
64-3/4" x 30" freestanding bath
K-8337

Features

- Freestanding design creates a striking focal point in your bathing area
- 17" (432 mm) depth offers a deep soaking experience
- Integral lumbar support
- Slotted overflow allows for deep soaking
- Center toe-tap drain with KOHLER Lithocast® cover

Material

- KOHLER Lithocast® Gloss cast resin

Installation

- Freestanding

Recommended Products/Accessories

K-23726 Drain treatment






Codes/Standards

CSA B45.5/IAPMO Z124

**KOHLER® Plastic Baths and Shower
Bases Lifetime Limited Warranty**

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Drain location:	Center
Basin area, bottom:	50" x 22-5/8" (1270 mm x 575 mm)
Basin area, top:	62-3/8" x 27-11/16" (1585 mm x 703 mm)
Weight:	318 lbs (144.2 kg)
Minimum floor load:	86.25 lbs/ft² (421.1 kg/m²)
Water depth:	17" (432 mm)
Water capacity:	92.3 gal (349.4 L)
Template:	Footprint, 1314998, not required, not included

Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Allow for 3" (76 mm) diameter of clearance around the drain pipe on finished floor material to prevent drain body interference during installation.