

# 33" top-/undermount single-bowl kitchen sink

K-8437-1

#### **Features**

- Single bowl
- 9-1/2" (241 mm) depth provides generous workspace
- Includes one faucet hole and option for three additional holes for knockout with ball-peen hammer and punch
- Includes K-6109 bottom sink rack
- Optional K-5376 bottom sink rack (sold separately)
- Matte finish offers rich, dimensional color

## Material

- KOHLER Neoroc® composite is durable and built to withstand day-to-day cleaning tasks
- Solid color throughout the sink
- Heat-resistant up to 750°F
- Scratch-, stain-, chip-, and thermal-shock-resistant

#### Installation

- 36" minimum base cabinet width for undermount or topmount installation
- Cutout templates included
- Top-mount or undermount

## **Recommended Products/Accessories**

K-5376 Sink Rack

K-6109 Sink Rack

K-8801 Sink drain and strainer with tailpiece

K-8799 Sink drain and strainer basket

K-23726 Drain treatment

K-23730 Neoroc® cleaner

# **Optional Products/Accessories**

K-11352 Disposal Flange with Stopper K-9000 P-Trap

# **Included Components**

K-6109 Sink Rack



# Codes/Standards

CSA B45.5/IAPMO Z124 IAPMO Certification

# KOHLER® Neoroc® Sinks Lifetime Limited Warranty

See website for detailed warranty information.

#### **Available Colors/Finishes**


Color tiles intended for reference only.


Color	Code	Description
	CM1	Matte Black
	СМЗ	Matte Taupe
	CM4	Matte Grey






33" top-/undermount single-bowl kitchen sink K-8437-1







# **Technical Information**

All product dimensions are nominal.

Basin configuration: Single Bowl Min. base cabinet 36" (914 mm)

width:

Bowl area: Length: 31-1/8" (791 mm)

Width: 16-15/16" (430 mm) Bowl depth: 9-1/2" (241 mm) Water depth: 9-1/2" (241 mm)

Number of deck

holes:

Drain hole: 3-7/8" (98 mm)

3

Template: 1281757-7, required, included

#### **Notes**

Install this product according to the installation instructions.

