

## Tea-for-Two® | K-852-JHE

60" x 32" drop-in/undermount whirlpool bath

### Features

- Six Proflex® hydromassage jets can be individually adjusted for water flow and direction
- Built-in heater
- Integral lumbar support
- Textured bottom surface
- Multiple pump location options give you more choices for installation and access
- Single-speed whirlpool offers performance and value, with six fully adjustable jets
- Safeguard® slip-resistant surface provides excellent traction underfoot



### Sustainability



### Available Colors/Finishes

*Color tiles intended for reference only.*

- 0 White
- 96 Biscuit
- 47 Almond
- NY Dune
- 7 Black Black



## Codes/Standards

ADA compliant when installed to the specific requirements of these regulations.



ASME A112.19.1/CSA B45.2  
ASME A112.19.7/CSA B45.10  
ASTM F462  
UL 1795  
CSA C22.2 No. 218.2  
ADA  
ICC/ANSI A117.1  
cUL Listed  
UL Listed

## Technical Information

All product dimensions are nominal.

Drain Location:	Reversible
Drain Hole Diameter:	2-3/16" (56 mm)
Minimum Flat for Door:	1-1/2" (38 mm)
Basin Area, Bottom:	40-1/2" x 20" (1029 mm x 508 mm)
Basin Area, Top:	52-3/4" x 24" (1340 mm x 610 mm)
Water Depth:	13-5/8" (346 mm)
Water Capacity:	60 gal (227.1 L)
Minimum Floor Load:	60 lbs/ft <sup>2</sup>
Weight:	290 lbs (131.5 kg)
Cutout:	Drop-in, 58-1/2" x 30-1/2" (1486 mm x 775 mm)

## Material

- KOHLER® enameled cast iron

## Recommended Products/Accessories

- K-1179 Tiling-in bead, 180" length
- K-586 Undermount kit for select 60" Tea-for-Two bath and whirlpool bath models
- K-1491 Bath/whirlpool pillow, removable
- K-1601 Bath/whirlpool footstep, removable
- K-23726 Drain treatment
- K-1172 Adjustable feet for use on Vintage®, Maestro™ and Tea-for-Two® 5' baths
- K-23725 Cast iron cleaner
- 1015255 Jet Trim Kit

## Required Products/Accessories

- K-23857 Bath drain trim
- or
- K-78440 33" cable pop-up bath drain

## Required Electrical Service

Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump:	120 V, 15 A, 60 Hz
Heater:	120 V, 15 A, 60 Hz

## Electrical Component Ratings


Pump:	120 V, 7 A, 60 Hz
Number of Speeds:	Single
Heater:	120 V, 12 A, 60 Hz

## Warranty

See website for detailed warranty information.

KOHLER® Hydrotherapy Components Five-Year Limited Warranty|KOHLER® Enameled Cast Iron Bath and Shower Base Lifetime Limited Warranty





## Installation

- Drop-in or undermount
- Reversible drain

## Installation Notes

*Install this product according to the installation instructions.*

Measure your actual product for rough-in details.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

ADA compliant when installed to the specific requirements of these regulations.

