

Features

- Relaxing multifunction showerhead offers wide soft coverage spray, slow pulse massage spray, and soft aerated spray settings
- 2.5 gpm (9.5 lpm) maximum flow rate
- Easy-grip ring offers smooth switching between spray options
- Flexible spray nozzles are easy to clean
- Includes wall supply elbow and vacuum breaker
- Includes MasterShower slidebar kit with acrylic soap dish, adjustable mounting bracket, and 60" metal shower hose

Material

- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount

Recommended Products/Accessories

- K-30646 Shower filter
- K-30647 Shower filter replacement
- K-23723 Faucet cleaner




OBC

Codes/Standards

ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992
OBC
IAPMO Certification

KOHLER[®] One-Year Limited Warranty

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Drain included: No

Handshower rated max flow: 2.5 gal/min (9.5 l/min)

Notes

For use with automatic compensating valves rated at 2.5 gal/min (9.5 l/min) or less.

Install this product according to the installation instructions.

OBC compliant when installed to the specific requirements of these regulations.