



Tea-for-Two®

66" x 36" drop-in BubbleMassage™ air bath
K-856-GC0



Features

- 40 airjets release thousands of bubbles that surround, support, and massage the body
- Variable-speed blower lets you adjust massage intensity to 18 levels
- Zones of Control™ feature allows you to target massage to back, midsection, or feet
- Chromatherapy lighting allows you to select a preferred color scheme to suit your mood
- Electronic keypad
- Spacious design accommodates up to two bathers
- Safeguard® slip-resistant surface provides excellent traction underfoot
- Automatic and manual purge cycles remove residual water from air channels after use

Material

- KOHLER® enameled cast iron

Hydrotherapy

- BubbleMassage™
- Chromatherapy

Installation

- Reversible drain
- Undermount
- Drop-in or undermount
- Requires cable pop-up bath drain and bath drain trim (sold separately)

Required Products/Accessories

K-23857 Bath drain trim
or
K-78440 33" cable pop-up bath drain

Recommended Products/Accessories

K-587 Under-Mount Installation Kit
K-1179 Vinyl Tiling-in Bead

Codes/Standards

ASME A112.19.1/CSA B45.2

ASME A112.19.7/CSA B45.10

ASTM F462

UL 1795

CSA C22.2 No. 218.2

cUL Listed


UL Listed

KOHLER® Enamelled Cast Iron Bath and Shower Base Lifetime Limited Warranty KOHLER® Hydrotherapy Components Five-Year Limited Warranty


See website for detailed warranty information.




Tea-for-Two®
66" x 36" drop-in BubbleMassage™ air bath
K-856-GC0



DISCONTINUED This product has been discontinued.



Blower Motor/Control Access
34" (864 mm) W x
15" (381 mm) H



Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

Kit is required for under-mount installations (sold separately).

If relocating the blower motor, do not relocate or alter the PVC tee or coiled flexible tubing connected to the blower. Follow the blower relocation instructions exactly. Provide access for servicing the blower.

Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Blower: 240 V, 15 A, 50/60 Hz

Technical Information

All product dimensions are nominal.

| | |
|------------------------------|---|
| Drain location: | Reversible |
| Basin area, bottom: | 45" x 25" (1143 mm x 635 mm) |
| Basin area, top: | 58" x 29" (1473 mm x 737 mm) |
| Weight: | 510 lbs (231.3 kg) |
| Minimum floor load: | 86 lbs/ft ² (419.9 kg/m ²) |
| Water depth: | 19-1/2" (495 mm) |
| Water capacity: | 105 gal (397.5 L) |
| Cutout: | Drop-in, 64-1/2" x 34-1/2" (1638 mm x 876 mm) |
| Template: | Under-mount, K-587, required, not included |
| Electrical component rating: | Blower: 240 V, 5 A, 50/60 Hz |

1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to www.kohler.com USA or www.kohler.ca Canada

2-15-2025 20:33 - US/CA

THE BOLD LOOK
OF **KOHLER**®