



## Tea-for-Two® 5.5' Whirlpool Bath K-856-HN

### Features

- 8 hydromassage jets can be individually adjusted for water flow and direction.
- Variable-speed pump for adjusting massage intensity.
- Built-in heater.
- Electronic keypad.
- Remote control.
- Spacious design accommodates up to two bathers.
- Safeguard® slip-resistant surface on bath floor.
- Multiple pump location options give you more choices for installation and access. (See specification sheet for pump locations.)
- End drain.

### Material

- KOHLER® enameled cast iron.

### Hydrotherapy

- Whirlpool.

### Installation

- Undermount.
- Drop-in or undermount.

### Required Products/Accessories

K-7147-AF 1-1/2" Contoured Pop-up Drain  
K-9698 Flexjet® Whirlpool Trim Kit

### Recommended Products/Accessories

K-1179 Vinyl Tiling-in Bead  
K-587 Under-Mount Installation Kit  
K-1703 Whirlpool Remote Control  
K-9497 2-1/2" Keypad Trim  
K-23726 Drain treatment  
K-23725 Cast iron cleaner



### Codes/Standards

ASME A112.19.1/CSA B45.2  
ASME A112.19.7/CSA B45.10  
ASTM F462  
UL 1795  
CSA C22.2 No. 218.2

### KOHLER® Enameled Cast Iron Bath and Shower Base Lifetime Limited Warranty


### KOHLER® Hydrotherapy Components Five-Year Limited Warranty

See website for detailed warranty information.


### Available Colors/Finishes

*Color tiles intended for reference only.*

| Color                                                                                | Code | Description   |
|--------------------------------------------------------------------------------------|------|---------------|
|  | 0    | White         |
|  | G9   | Sandbar       |
|  | 33   | Mexican Sand™ |
|  | K4   | Cashmere      |



No change in measurements if connected with drain illustrated. (K-7147-AF)



### Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump, Heater: 240 V, 20 A, 50/60 Hz

### Technical Information

All product dimensions are nominal.

|                              |                                                 |
|------------------------------|-------------------------------------------------|
| Installation:                | Drop-in, Under-mount                            |
| Drain location:              | End                                             |
| Basin area, bottom:          | 45" x 25" (1143 mm x 635 mm)                    |
| Basin area, top:             | 58" x 29" (1473 mm x 737 mm)                    |
| Weight:                      | 510 lbs (231.3 kg)                              |
| Minimum floor load:          | 86 lbs/ft² (419.9 kg/m²)                        |
| Water depth:                 | 19-1/2" (495 mm)                                |
| Water capacity:              | 105 gal (397.5 L)                               |
| Cutout:                      | Drop-in, 64-1/2" x 34-1/2" (1638 mm x 876 mm)   |
| Template:                    | Under-mount, K-587, required, not included      |
| Electrical component rating: | Pump: 240 V, 11 A<br>Heater: 240 V, 6 A, 1500 W |

### Notes

Measure your actual product for rough-in details. Install this product according to the installation instructions.

The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

The pump must be relocated to a custom position at the time of installation. Provide adequate clearance.

Kit is required for under-mount installations (sold separately).

Cast iron whirlpools are extremely heavy, making some drop-in installations difficult. Splitting the deck/surround is recommended if installing into a deck.