



Tea-for-Two® | K-856-JLH

66" x 36" alcove whirlpool bath with left drain

Features

- Six Proflex® hydromassage jets can be individually adjusted for water flow and direction
- Built-in heater
- Spacious design accommodates up to two bathers
- Integral lumbar support
- Textured bottom surface
- Single-speed whirlpool offers performance and value, with six fully adjustable jets
- Safeguard® slip-resistant surface provides excellent traction underfoot



Sustainability



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 01:54 - US-CA

THE BOLD LOOK
OF **KOHLER**®

Codes/Standards

ADA compliant when installed to the specific requirements of these regulations.



ASME A112.19.1/CSA B45.2
ASME A112.19.7/CSA B45.10
ASTM F462
UL 1795
CSA C22.2 No. 218.2
ADA
ICC/ANSI A117.1
cUL Listed
UL Listed

Technical Information

All product dimensions are nominal.

Drain Location:	Left
Drain Hole Diameter:	2-1/4" (56 mm)
Minimum Flat for Door:	2-1/4" (57 mm)
Basin Area, Bottom:	40-1/2" x 20" (1029 mm x 508 mm)
Basin Area, Top:	52-3/4" x 24" (1340 mm x 610 mm)
Water Depth:	13-5/8" (346 mm)
Water Capacity:	60 gal (227.1 L)
Minimum Floor Load:	60 lbs/ft ²
Weight:	290 lbs (131.5 kg)
Cutout:	Drop-in, 58-1/2" x 30-1/2" (1486 mm x 775 mm)

Material

- KOHLER® enameled cast iron

Recommended Products/Accessories

- K-1179 Tiling-in bead, 180" length
- K-586 Undermount kit for select 60" Tea-for-Two bath and whirlpool bath models
- K-1491 Bath/whirlpool pillow, removable
- K-1601 Bath/whirlpool footstop, removable
- K-23726 Drain treatment
- K-1172 Adjustable feet for use on Vintage®, Maestro™ and Tea-for-Two® 5' baths
- K-23725 Cast iron cleaner

Required Products/Accessories

- K-9696 Whirlpool trim kit with six jets
- or
- K-23857 Bath drain trim
- or
- K-78440 33" cable pop-up bath drain

Required Electrical Service

Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump:	120 V, 15 A, 60 Hz
Heater:	120 V, 15 A, 60 Hz

Electrical Component Ratings

Pump:	120 V, 7 A, 60 Hz
Number of Speeds:	Single
Heater:	120 V, 12 A, 60 Hz




Warranty

See website for detailed warranty information.

KOHLER® Hydrotherapy Components Five-Year Limited
Warranty|KOHLER® Enameled Cast Iron Bath and Shower
Base Lifetime Limited Warranty



1-800-4KOHLER (1-800-456-4537)
Kohler Co. reserves the right to make revisions without notice to product specifications.
For the most current specification sheet, go to www.kohler.com USA or www.kohler.ca Canada.
7-30-2026 01:54 - US-CA



Installation

- Alcove
- Left drain

Installation Notes

Install this product according to the installation instructions.

Measure your actual product for rough-in details.
The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.
ADA compliant when installed to the specific requirements of these regulations.

