

## Tea-for-Two® | K-865-JHD

71-3/4" x 36" drop-in/undermount whirlpool bath

### Features

- Six Proflex® hydromassage jets can be individually adjusted for water flow and direction
- Built-in heater
- Spacious design accommodates up to two bathers
- Integral lumbar support
- Multiple pump location options give you more choices for installation and access
- Textured bottom surface
- Single-speed whirlpool offers performance and value, with six fully adjustable jets



### Sustainability



### Available Colors/Finishes

*Color tiles intended for reference only.*

- 0 White
- 96 Biscuit
- 47 Almond
- NY Dune
- 7 Black Black



## Codes/Standards

ASME A112.19.1/CSA B45.2  
ASME A112.19.7/CSA B45.10  
ASTM F462  
UL 1795  
CSA C22.2 No. 218.2  
cUL Listed  
UL Listed

## Technical Information

*All product dimensions are nominal.*

Drain Location:	Reversible
Drain Hole Diameter:	2-3/16" (56 mm)
Minimum Flat for Door:	2-1/8" (53 mm)
Basin Area, Bottom:	49" x 22" (1245 mm x 559 mm)
Basin Area, Top:	62" x 28" (1575 mm x 711 mm)
Water Depth:	17" (432 mm)
Water Capacity:	89 gal (336.9 L)
Minimum Floor Load:	69 lbs/ft <sup>2</sup>
Weight:	455 lbs (206.4 kg)
Cutout:	Drop-in, 70-1/4" x 34-1/2" (1784 mm x 876 mm)

## Material

- KOHLER® enameled cast iron

## Recommended Products/Accessories

K-582 Undermount kit for select 72" Tea-for-Two bath models  
K-1179 Tiling-in bead, 180" length  
K-23726 Drain treatment  
K-23725 Cast iron cleaner  
1015255 Jet Trim Kit

## Required Products/Accessories

- K-23857 Bath drain trim
- or
- K-78440 33" cable pop-up bath drain

## Required Electrical Service

Two dedicated circuits required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Pump:	120 V, 15 A, 60 Hz
Heater:	120 V, 15 A, 60 Hz

## Electrical Component Ratings


Pump:	120 V, 7 A, 60 Hz
Number of Speeds:	Single
Heater:	120 V, 12 A, 60 Hz

## Warranty


*See website for detailed warranty information.*

KOHLER® Hydrotherapy Components Five-Year Limited Warranty|KOHLER® Enameled Cast Iron Bath and Shower Base Lifetime Limited Warranty







No change in measurements if connected with drain illustrated. (K-23856-NA)



**Drop-in Rim Detail**



**Installation**

- Drop-in or undermount
- Reversible drain

**Installation Notes**

*Install this product according to the installation instructions.*

Measure your actual product for rough-in details.  
The hot water supply should be 70% of the capacity of the bath or greater. Installations will vary.

