

27" undermount single-bowl workstation kitchen sink K-8668-5UPC

Features

- 30" (762 mm) minimum base cabinet width
- Single bowl
- 9" (229 mm) depth provides generous workspace
- Five oversized faucet holes
- Oversized holes allow for easy installation of faucets and accessories
- Bowl slopes toward drain to minimize water pooling
- Offset drain increases workspace in the sink and storage space underneath
- Included accessories: cutting board, drain board, colander / drying rack, soaking bin with drain, stainless steel bottom sink rack
- Drain board, colander / drying rack, soaking bin with drain, and bottom sink rack are dishwasher-safe
- Sink drain with strainer sold separately



KOHLER® enameled cast iron

Installation

Undermount

Recommended Products/Accessories

K-8801 Sink drain and strainer with tailpiece

K-8799 Sink drain and strainer basket

K-23726 Drain treatment

K-23725 Cast iron cleaner

K-35007 Bifold multipurpose rack

K-35002 Ice bucket holder

K-35003 Workstation sink cover

K-35004 HDPE cutting board

K-35005 Marble serving tray

K-35487 Three-piece ice bucket set

K-35484 Three-piece workstation sink prep bowl set

Optional Products/Accessories

K-11352 Disposal Flange with Stopper

K-9000 P-Trap

Included Components

K-35000 Three-piece workstation sink accessory set

K-35001 Maple wood cutting board

K-9137 Sink Rack



Codes/Standards

ASME A112.19.1/CSA B45.2

KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes


Color tiles intended for reference only.


Color	Code	Description
	0	White
	FF	Sea Salt™
	96	Biscuit
	NY	Dune
	95	Ice™ Grey
	58	Thunder™ Grey
	7	Black Black™
	TRF	Truffle





27" undermount single-bowl workstation kitchen sink K-8668-5UPC





Technical Information

All product dimensions are nominal.

Basin configuration: Single Bowl Center(s): 8" (203 mm) Min. base cabinet 30" (762 mm)

width:

Bowl area (Basin Length: 24-1/4" (616 mm) #1): Width: 15-13/16" (402 mm)

5

Bowl depth: 9" (229 mm) Water depth: 9" (229 mm)

Number of deck

holes:

Faucet hole(s): 2-3/8" (60 mm)

Drain hole: 3-7/8" (98 mm)

Template: Undermount, 1244382-7, required,

included

Notes

Install this product according to the installation instructions.

NOTICE: Countertop manufacturer or cutter must use the cut-out template provided with the product, or a current one provided by Kohler Co. (call 1-800-4KOHLER). Kohler Co. is not responsible for cutout errors when the incorrect cut-out template is used



