

33" top-mount double-bowl workstation kitchen sink K-8679-1A2

Features

- 33" (838 mm) minimum base cabinet width
- Double-equal bowls
- 9" (229 mm) depth provides generous workspace
- Single faucet hole
- Bowl slopes toward drain to minimize water pooling
- Offset drains increase workspace in the sink and storage space underneath
- Includes K-6239 colander with integral cutting board and K-9238 bottom sink rack



KOHLER® enameled cast iron

Installation

Top-mount

Recommended Products/Accessories

K-8801 Sink drain and strainer with tailpiece (Qty 2)

K-9238 Sink Rack

K-8799 Sink drain and strainer basket

K-23726 Drain treatment

K-23725 Cast iron cleaner

Optional Products/Accessories

K-11352 Disposal Flange with Stopper K-9000 P-Trap

Included Components

K-6239 Colander with Cutting Board K-9238 Sink Rack



Codes/Standards

ASME A112.19.1/CSA B45.2 IAPMO Certification

KOHLER® Enameled Cast Iron Kitchen and Bathroom Sink Lifetime Limited Warranty

See website for detailed warranty information.


Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	0	White
	96	Biscuit
	7	Black Black™



33" top-mount double-bowl workstation kitchen sink K-8679-1A2



Technical Information

All product dimensions are nominal.

Basin configuration: Equal Bowls
Min. base cabinet 33" (838 mm)

width:

Bowl area (Double Length: 14-5/16" (363 mm) Equal Basins): Width: 15-13/16" (402 mm)

Bowl depth: 9" (229 mm) Water depth: 9" (229 mm)

Drain hole: 3-7/8" (98 mm)

Template: 1166727-7, required, included

Notes

Install this product according to the installation instructions.

