

### Features

- For sink installations with 3-1/2" (89 mm) or 4" (102 mm) outlet
- Removable basket strainer with open/close stopper that seals tightly
- Less tailpiece
- 4-1/2" (114 mm) x 2-7/8" (73 mm)

### Material

- Solid-brass construction for durability and reliability

### Recommended Products/Accessories

- K-23726 Drain treatment
- K-23723 Faucet cleaner



### Codes/Standards









ASME A112.18.2/CSA B125.2


### KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	CP	Polished Chrome
	SN	Vibrant® Polished Nickel
	BN	Vibrant® Brushed Nickel
	VS	Vibrant® Stainless
	BV	Vibrant® Brushed Bronze
	BL	Matte Black
	2MB	Vibrant® Brushed Moderne Brass
	TT	Vibrant Titanium



### Technical Information

All product dimensions are nominal.

Drain included: Yes

### Handshower:

Rated maximum flow: 0 gal/min (0 l/min)