



# Duostrainer®

Sink drain body with tailpiece  
**K-8804**

## Features

- For sink installations with 3-1/2" (89 mm) or 4" (102 mm) outlet
- Quick-locking installation system
- 1-1/2" (38 mm) diameter connection and brass 4" (102 mm) tailpiece
- Combines with the K-8803 sink basket strainer (sold separately)

## Material

- Solid-brass construction for durability and reliability

## Required Products/Accessories

K-8803 Manual Sink Basket Strainer

## Recommended Products/Accessories

K-23726 Drain treatment

K-23723 Faucet cleaner



## Codes/Standards

ASME A112.18.2/CSA B125.2

IAPMO Certification

## KOHLER® One-Year Limited Warranty

See website for detailed warranty information.

## Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
-------	------	-------------

	CP	Polished Chrome
---	----	-----------------


1-800-4KOHLER (1-800-456-4537)

Kohler Co. reserves the right to make revisions without notice to product specifications.

For the most current Specification Sheet, go to [www.kohler.com](http://www.kohler.com) USA or [www.kohler.ca](http://www.kohler.ca) Canada

11-3-2024 23:56 - US/CA

THE BOLD LOOK  
OF **KOHLER®**



### Technical Information

All product dimensions are nominal.

Material: Brass

### Notes

Install this product according to the installation guide.