

#### Features

- Spacious shower base offers ample room for showering
- Safeguard® slip-resistant surface provides excellent traction underfoot
- Single threshold for alcove installation with three tile-in flanges

#### Material

- KOHLER® enameled cast iron

#### Installation

- Left drain

#### Recommended Products/Accessories

- K-9132 Shower Drain
- K-706009-D3 Frameless Sliding Shower Door
- K-706009-L Frameless Sliding Shower Door
- K-706015-D3 Frameless Sliding Shower Door
- K-706015-L 74" H sliding shower door with 1/4"-thick glass
- K-5526 7 kW steam generator
- K-5557 steam generator control kit
- K-23726 Drain treatment
- K-23725 Cast iron cleaner



#### Codes/Standards






- ASME A112.19.1/CSA B45.2
- ASTM F462
- IAPMO Certification


#### KOHLER® Enameled Cast Iron Bath and Shower Base Lifetime Limited Warranty

See website for detailed warranty information.

#### Available Colors/Finishes

*Color tiles intended for reference only.*

Color	Code	Description
	0	White
	96	Biscuit
	NY	Dune
	58	Thunder™ Grey
	7	Black Black™



## Technical Information

All product dimensions are nominal.

Drain location:	Left
Weight:	193 lbs (87.5 kg)
Minimum floor load:	40 lbs/ft <sup>2</sup> (195.3 kg/m <sup>2</sup> )
Minimum flat for door:	2-7/8" (73 mm)

## Notes

Measure your actual product for rough-in details.

Install this product according to the installation instructions.

Shimming may be required to level the fixture.

Shimming may be required between the stud frame and the fixture.

Stud opening tolerance is + 1/4" (6 mm), - 0" (0 mm).

KOHLER steam generator/control kit is designed for use with this product. Kohler Co. shall not be responsible for problems encountered due to the installation and use of other manufacturer's steam generators.