

Features

- Pressure-compensating flow control to deliver a splatter-free column of water
- 0.95" (24 mm) orifice to optimize performance
- Easy-to-access cartridge for cleaning and replacement
- Complements Purist faucets and accessories

Material

Solid-brass construction for durability and reliability

Installation

Wall- or ceiling-mount

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards

ASME A112.18.1/CSA B125.1 All applicable US Federal and State material regulations IAPMO Certification

KOHLER[®] Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.


Color Code Description





KOHLER. Faucets


Wall- or -ceiling-mount bath filler K-923



Technical Information

All product dimensions are nominal. Drain included: No

Spout:



Notes

Install this product according to the installation guide.

For ceiling-mount installation, product must be mounted a maximum of 9' (2.7 m) above the bath/whirlpool floor.

Drip tray (K-924) is an optional accessory available for wall-mount installation only. Ensure a minimum of 36" (914 mm) of straight piping prior to the spout.

When a deck mounted transfer valve (K-408-K or K-409-K) is used for a ceiling mount, install a check valve between the spout and the diverter In applications where excessive air could enter the water supply, install an air separator to eliminate air bubbles.

Flow rate is 7-15 gal/min (26.5-56.8 l/min)]. Splashing may occur if the flow rate is less than 5 gal/min (18.9 l/min).

