

Features

- Single-function hygiene spray delivers a full, consistent stream, regardless of water pressure
- Soft spray pattern
- Ergonomic button design
- 2.25 gpm (8.5 lpm) maximum flow rate at 43.5 psi (3 bar)
- Includes 47.24 inch (1200 mm) hose and wall-mount holder
- Includes a screen washer to prevent clogging

Material

- Premium material construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation

- Wall-mount
- G 1/2 connection



Codes/Standards






None Applicable


KOHLER® India Faucet, Sanitaryware and Bathing Products Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome
	AF	Vibrant® French Gold
	BN	Vibrant® Brushed Nickel
	BV	Vibrant® Brushed Bronze
	BL	Matte Black



Technical Information

All product dimensions are nominal.

Notes

Install this product according to the installation guide.