

Features

- Versatile, contemporary design
- Single Lever handle allows for on/off activation, volume, and temperature control
- 5.8 inch (148 mm) spout reach
- 3.5 inch (89 mm) spout height
- Laminar flow
- 1.8 gpm (7.0 lpm) maximum flow rate at 43.5 psi (3.0 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Includes pop-up drain with lift rod and 1.25 inch (32 mm) tailpiece

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Deck-mount



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Faucet flow rate: 2.2 gal/min (8.3 l/min)

Drain included: Yes

Drain tailpiece included: Yes

Spout:

Spout reach: 5-13/16\" (148 mm)

Notes

Install this product according to the installation instructions.