

Features

- Single Lever handle allows for on/off activation, volume, and temperature control
- 8.9 inch (227 mm) spout reach
- 7.5 gpm (28.4 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)
- Shift+™ Round multifunction handshower offers full coverage and targeted massage spray options
- 59 inch (1500 mm) handshower hose
- 2.5 gpm (9.5 lpm) maximum handshower flow rate at 80 psi (5.5 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Coordinates with other products in the Avid collection

Material


- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Floor-mount
- Requires floor-mount bath filler mounting base (sold separately)

Required Products/Accessories

K-97904T



Codes/Standards



None Applicable

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Faucet flow rate: 4.5 gal/min (17 l/min)

Spout:

Spout reach: 8-7/8" (226 mm)

Shower/Rainhead rated max flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation instructions.