

Features

- Panel utilizes an integrated system of four 22-nozzle, fully adjustable sprayheads for stimulating hydrotherapy
- Low-profile design complements any decor
- MasterClean™ sprayface features an easy-to-clean surface that withstands mineral buildup and maximizes spray performance
- 0.6 gpm maximum flow rate from each sprayhead for a maximum combined flow of 2.4 gpm
- 1/2" NPT connections

Material


- KOHLER finishes resist corrosion and tarnishing

Installation

- Ceiling-mount
- Soldering template included for ease of installation

Recommended Products/Accessories

K-23723 Faucet cleaner



Codes/Standards



ASME A112.18.1/CSA B125.1
DOE - Energy Policy Act 1992




KOHLER[®] Faucet Lifetime Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

| Color | Code | Description |
|---|------|--------------------------------------|
|  | CP | Polished Chrome |
|  | SN | Vibrant [®] Polished Nickel |
|  | BN | Vibrant [®] Brushed Nickel |
|  | BV | Vibrant [®] Brushed Bronze |
|  | 2BZ | Oil-Rubbed Bronze |
|  | BL | Matte Black |



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2.4 gal/min (9.1 l/min)

Spout:

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

Showerhead/Body Spray:

Rated maximum flow: 2.5 gal/min (9.5 l/min)

Notes

Install this product according to the installation guide.