

## Features

- Single lever handle allows for both on/off activation and temperature setting
- 6-1/4" (159 mm) spout reach
- 10-1/2" (267 mm) spout height
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- Laminar flow delivers a graceful stream of water
- Red/blue indexing
- Includes valve
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Includes pop-up drain
- Part of the Aleo bathroom faucet and showering collection
- G 3/8" connection

## Material


- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

## Installation

- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation

## Recommended Products/Accessories

K-23726 Drain treatment  
K-23723 Faucet cleaner




## Codes/Standards

None Applicable

## KOHLER® Faucet Lifetime Limited Warranty

See website for detailed warranty information.



### Technical Information

All product dimensions are nominal.

#### Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Pressure: 60 psi (4.1 bar)

Drain included: Yes

Drain with overflow: Yes

#### Spout:

Spout reach: 6-5/16" (160 mm)

### Notes

Install this product according to the installation instructions.