

Features


- Single Lever handle allows for on/off activation, volume, and temperature control
- Red/blue indexing
- 10-1/2" (267 mm) spout height
- 6-1/4" (159 mm) spout reach
- Tall height is ideal for vessel-style sinks
- Laminar flow
- 1.2 gpm (4.5 lpm) maximum flow rate at 45 psi (3.1 bar)
- Includes valve
- KOHLER ceramic disc valves exceed industry longevity standards by over two times, ensuring durable performance for life
- Includes pop-up drain
- Part of the Aleo bathroom faucet and showering collection
- G 3/8" connection

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation


- Deck-mount
- For single-hole installation
- Flexible supply lines simplify installation



Codes/Standards

None Applicable

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet flow rate: 1.2 gal/min (4.5 l/min)

Drain included: Yes

Notes

Install this product according to the installation guide.