

Features

- Contemporary design
- Integral pull-out sprayhead with retractable hose
- Aerated flow delivers a smooth, steady stream of water
- Single lever handle is simple to use and makes adjusting water temperature easy
- Red/blue indexing on handle
- 10-1/8" (257 mm) spout height
- 2.2 gpm (8.3 lpm) maximum flow rate at 60 psi (4.14 bar)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER® finishes resist corrosion and tarnishing

Installation


- Single-hole installation (escutcheon plate sold separately)
- Deck-mount
- Supply line sold separately



Codes/Standards

Plumbing Standards
GB 18145

See website for detailed warranty information.



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 2.2 gal/min (8.3 l/min)

Drain included: No

Spout:

Spout reach: 8-11/16" (221 mm)

Notes

Install this product according to the installation instructions.