

Features

- The vintage artisan inspired top-mount handle provides a unique statement to any kitchen
- KOHLER[®] ceramic disc valves exceed industry longevity standards for a lifetime of durable performance
- Single lever handle is simple to use and makes adjusting water temperature easy
- Temperature memory allows faucet to be turned on and off at the temperature set during prior usage
- 1.5 gpm (5.7 lpm) maximum flow rate at 60 psi (4.14 bar)

Material

- Premium metal construction for durability and reliability

Installation

- Flexible connections for easy installation
- Single-hole installation

Adapters, Rough-in and Extension Kits

1012715

Range: 3-1/4" (83 mm) -
5-3/8" (137 mm)

Recommended Products/Accessories

K-77685 Single-cartridge water filtration system

K-77686 Double-cartridge water filtration system

K-77687 single replacement filter cartridge

K-77688 Replacement Filter Cartridges, Two-Pack

K-23723 Faucet cleaner



Codes/Standards

ASME A112.18.1/CSA B125.1

NSF/ANSI/CAN 61

NSF/ANSI/CAN 372

All applicable US Federal and State material regulations

DOE - Energy Policy Act 1992

California Energy Commission (CEC)

IAPMO Certification

KOHLER[®] Faucet Lifetime Limited Warranty


See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color Code Description

	CP	Polished Chrome
	SN	Vibrant [®] Polished Nickel
	AF	Vibrant [®] French Gold
	VS	Vibrant [®] Stainless
	BV	Vibrant [®] Brushed Bronze
	BL	Matte Black
	2MB	Vibrant [®] Brushed Moderne Brass
	TT	Vibrant Titanium



Technical Information

All product dimensions are nominal.

Faucet:

Flow rate: 1.5 gal/min (5.7 l/min)

Drain included: No

Spout:

Spout reach: 7-5/16" (186 mm)

Handshower:

Rated maximum flow: 0 gal/min (0 l/min)

Notes

Install this product according to the installation guide.