

Features

- Contemporary design
- High-arch gooseneck spout and 360° spout rotation offer superior clearance for filling pots and cleaning
- Single lever handle provides on/off activation and volume control
- Aerated flow
- For use with cold water line only
- 7.3 gpm (27.6 lpm) maximum bath faucet flow rate at 45 psi (3.1 bar)

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome



Technical Information

All product dimensions are nominal.

Notes

Install this product according to the installation guide.