

Features

- Contemporary design
- Arched spout and spout rotation offer superior clearance for filling pots
- Single Lever handle allows for on/off activation, volume, and temperature control
- Red/blue indexing on handle
- Aerated flow
- 22.0 lpm (5.5 gpm) maximum flow rate at 3.0 bar (43.5 psi)
- KOHLER® ceramic disc valves exceed industry longevity standards for a lifetime of durable performance

Material

- Premium metal construction for durability and reliability
- KOHLER finishes resist corrosion and tarnishing

Installation

- Wall-mount



Codes/Standards

None Applicable


KOHLER® India Faucet Limited Warranty

See website for detailed warranty information.

Available Colors/Finishes

Color tiles intended for reference only.

Color	Code	Description
	CP	Polished Chrome

**Technical Information**

All product dimensions are nominal.

Notes

Install this product according to the installation instructions.