

## Verdera® | K-99573-VLAN

40" x 33" lighted mirror with Amazon Alexa

### Features

- Well-designed seamless integration of Amazon Alexa minimizes clutter and delivers optimal interaction
- Amazon Alexa-enabled so you can ask to play music, hear the news, check weather, control smart home devices, and more
- Integrated stereo sound system fills the room with complete sound quality
- Built-in microphone for voice control interaction
- Voice control of optimally bright task lighting on/off, brightness, and sound volume
- 2200 lumen brightness ensures consistent lighting with no hot spots or dark spots
- Approx. 3000 Kelvin light appearance delivers a neutral light ideal for overall bathroom aesthetics as well as tasks
- Greater than 90 CRI\* lets you see yourself in the truest light for makeup application, grooming, and skin care
- High-efficiency LED achieves over 65 lumens/watt\*
- Built-in dimmer
- Integrated LED bulbs have an estimated life expectancy of 36,000 hours
- Down-firing way-finding light brightens via proximity sensor
- Pivoting side panels allow you to direct light for specific tasks
- Syncs with devices enabled with BLUETOOTH® wireless technology including smartphones, MP3 players, tablets, and laptops located up to 33 feet (10 meters) away



---

## Codes/Standards

CA Title 24 JA8  
cUL Listed  
UL Listed

---

## Technical Information

*All product dimensions are nominal.*

Lighting Included: Yes  
Mirror Type: Polished Edge

---

## Material

- Anodized aluminum construction with a durable rustproof and chip-resistant finish
- 

## Recommended Products/Accessories

K-23723 Faucet cleaner

---

## Connectivity



The BLUETOOTH® word mark and logos are registered trademarks owned by Bluetooth SIG, Inc. and any use of such marks by Kohler Co. is under license.

---

## Required Electrical Service

One dedicated circuit required, protected with Class A Ground-Fault Circuit-Interrupter (GFCI). Outside North America, this device may be known as a Residual Current Device (RCD).

Lights: 120 V, 15 A, 60 Hz

## Electrical Component Ratings

Lights: 120 V, 0.3 A, 60 Hz, 36 W,  
2200 Lumens


---

## Warranty

*See website for detailed warranty information.*

KOHLER® One-Year Limited Warranty





## Installation

- Includes mounting hardware for surface installation

## Installation Notes

*Install this product according to the installation instructions.*

Select the type of fastener based on the wall material. A minimum 20 lb (9.07 kg) load bearing fastener is recommended.

Install the fastener to a stud to avoid possible property and product damage.

